

Flexible Cables

HKLJ-Ø 300/300 V



Application

Halogen-free and fire retardant Flexible cable for appliances, devices and lamps as well as for internal wiring. Not suitable for outdoor application. Must be installed according to S.B.

Standard

HD 308 S2
EN 50267-1
EN 61034-1-2
IEC 60332-1-2

Color marking of conductors
Hologen free material

Vertical flame propagation for a single insulated wire or cable

Temperature

Maximum operating Temperature 60°C

Features

Bending radius 6xD

Conductors and screen area [mm ²]	Outer Sheath Colour	Diameter over sheath [mm]	Cable weight [kg/km]	Standard delivery length [m]	Delivery Package	E-number
2x0,75	White	5,5	40	100	S100	
3x0,75	White	5,8	45	100	S100	