


## Power Cables 1kV

# PEX-M-AL 1 kV



### Application

Halogen free cable.  
Suitable for installation outdoors in cable trough and directly in soil.  
Suitable for plowing.

### Flame retardance

Flame retardant - Not applicable

### Standard

IEC 60228	Conductor standard
IEC 60502-1	Construction Standard
CENELEC HD 603 Part 5 Section B	Harmonized construction standard

### Construction

Conductors	Solid sector shaped aluminum core acc. to IEC 60228 class 1
Conductor Insulation	XLPE, halogen-free
Marking of cores	Light Blue, Brown, Black and Grey
Inner covering	Plastic tape
Outer Sheath	UV-stabilized halogen-free PE, grey
Example of marking on sheath	PEX-M-AL 1 kV PRYSMIAN "Date and time", meter marked

### Temperature

Maximum operating Temperature	90°C
Temperatures at installation [°C]	Minimum -15 °C

### Features

Additional Feature Information	4 kV AC
Bending radius	During installation: 10xD Final installation: 8xD
Max Pulling force - pulling grip [N/mm <sup>2</sup> ]	25 N/mm <sup>2</sup>

### Electrical

Test Voltage [kV]	4 kV AC
-------------------	---------

Conductors and screen area [mm <sup>2</sup> ]	Diameter over sheath [mm]	Cable weight [kg/km]	Standard delivery length [m]	Delivery Package	SAP Number
4x50	26,0	760	1000	T 1400	20102474
4x95	34,0	1375	1000	T 1700	20102475
4x150	41,5	2075	1000	T 2100	20102476
4x240	51,5	3305	1000	T 2400 / K26	20102477