


## Overblow Duct Optical Mini-Cable

### Cable Design

IEC/EN 60794



- not to scale -

- **Optical fibre:** Singlemode 200µm G.657.A2.
- **Central strength member (CSM):** Glass fibre reinforced plastic material (GRP) with over-sheathing.
- **Tube:** Thermoplastic material, containing 12 Singlemode optical fibres and filled with a suitable water tightness compound.
- **Stranding:** The required number of elements (tubes or fillers) are SZ stranded in two layers around the central strength member.
- **Longitudinal Water Tightness:** Water swellable elements (dry core).
- **Outer Sheath:** HDPE, 2 Ripcords beneath the sheath.

This loose tube optical cable is designed for outdoor installation in occupied ducts by overblow blowing techniques.

### Technical data

No. of Fibres		432		
Design	Part No	60073562		
Layout (tubes x Fibre)		36x12		
Loose Tube / Filler - Ø	mm	1.3		
CSM/sheath diameter	mm	3.5/5.4		
Sheath thickness	mm	0.9		
Cable Diameter	mm	12.8		
Cable Weight	kg / km	135		
Max installation tension	N	1350 (1xW)		
Min. bending radius	mm	Without Tension 15 x Cable-Ø	Under Maximum Tension 20 x Cable-Ø	
Temperature range	°C	Installation -20 -> +45;	Transport. & Storage -30 -> +70;	Operation -20 -> +70;

Please refer to Overblow Installation Procedure (Contact for info), General Installation (Datasheet Ref: CIG031) and Safety & Handling recommendations (Generic Optical cable MSDS - Datasheet Ref: 9980-02-1) before handling.

### Main characteristics

Test	Standard	Value	Requirement*
Maximum Tension at installation (short term)	IEC 60794-1-21-E1	1W (see table above)	Fibre strain ≤ 0.6%, Δα reversible
Crush	IEC 60794-1-21-E3A	2000N	Δα ≤ 0.05 dB, cable integrity
Impact	IEC 60794-1-21-E4	5Nm, 3 impacts, r=300mm	Δα ≤ 0.05 dB
Repeated bending	IEC 60794-1-21-E6	R = 20 x cable Ø, 10N, 35 cycles	cable integrity
Torsion	IEC 60794-1-21-E7	100N, ± 360°, 10 cycles, 2m	Δα ≤ 0.05 dB, cable integrity
Kink	IEC 60794-1-21-E10	R = 15 x cable Ø	cable integrity
Cable bend	IEC 60794-1-21-E11	R = 15 x cable Ø	Δα ≤ 0.05 dB, cable integrity
Temperature range	IEC 60794-1-22-F1	-20°C to +70°C	Δα ≤ 0.15 dB/km
Water Penetration	IEC 60794-1-2-F5B	sample=3m, water column=1m	No water leakage after 24 hours
Ageing	IEC 60794-1-2-F9	168 hours, 85°C	Δα ≤ 0.25 dB/km; ≤ 0.15 dB/km ave.

\*all optical measurements performed at 1550 nm

## Optical Characteristics

See Optical Fibre Datasheet Ref: Singlemode 200µm G.657.A2 (HE).

## Identification

### Fibre Colours

No.	1	2	3	4	5	6	7	8	9	10	11	12
Colour	Blue	Orange	Green	Red	Grey	Yellow	Brown	Violet	Black	White	Pink	Turquoise

### Buffer Tube Colours

#### 1<sup>st</sup> Layer

	Pilot	Intermediate	Marker
Colour	Red	White	Green

#### 2<sup>nd</sup> Layer

	1	2	3
Colour	Red	White	Green

### Sheath Colour:

The outer sheath colour is black.

### Sheath Marking:

The outer sheath is marked in 1 metre intervals as follows:



## Installation

### Duct:

Designed to be installed by blowing into occupied miniduct.

## Logistic

### Packing:

Wooden drums with protection.

### Delivery Lengths:

Standard delivery length is 2km.

Maximum delivery length is 4km.

© PRYSMIAN 2018, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian: any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian in accordance with Prysmian UK Quality Plan QP0000 latest issue.