


## UC400 23 Cat. 6 U/UTP LSHF d64 Cca

### U/UTP AWG23/1 Installation Cable



## Application

Primary (Campus), Secondary (Riser), Tertiary (Horizontal)  
IEEE 802.3: 10Base-T; 100Base-T; 1000Base-T;  
IEEE 802.5 16 MB; ISDN; TPDDI; ATM  
Power over Ethernet (PoE) / Type 1-4

## Standards

EIA/TIA-568-C.2  
ISO/IEC 11801.; IEC 61156-5  
EN 50173-1, EN 50288-6-1  
IEEE 802.3af / at / bt

## Flame resistance

EN 50399: Class C<sub>ca</sub>s1a d1 a1  
LSHF-FR Cca (FRNC-C): IEC60332-3-24; IEC 60332-1; 60754-2; IEC 61034;

## Construction

Conductor	bare copper wire Ø 0.56 mm (AWG23/1)
Insulation	Polyethylene, Ø 1.0 mm
Twisting	2 cores to the pair
Cable lay up	4 pairs to the core non metallic cross separator (spline)
Sheath	LSHF-FR (FRNC, LSOH), blue RAL 5012

## Mechanical properties

Minimum bending radius	Installation	8 x D
	Installed	4 x D
Temperature range	during operation	-20°C up to + 60°C
	during installation	0°C up to + 50°C

## UC400 23 Cat. 6 U/UTP LSHF d64 Cca

### Electrical properties

at 20°C

DC loop resistance	154 Ω/km
Resistance unbalance	≤ 2%
Insulation resistance (500 V)	≥ 5000 MΩ *km
Capacitance at 800 Hz	Nom. 48 nF/km
Capacitance unbalance (pair to ground)	≤ 1500 pF/km
Mean impedance 100 MHz	100 ± 5 Ω
Nominal velocity of propagation	Approx. 67 %
Propagation delay	Nominal 535 ns/100m
Delay skew	Nominal 20 ns/100m
Test voltage (DC, 1 min)	1000 V
Core/Core	
Coupling attenuation	≥ 40 dB

### Transmission characteristics acc. to Category 6

at 20°C

f (MHz)	Attenuation (dB/100m)		NEXT (dB)		PS-NEXT (dB)		ACR (dB/100m)		PS-ACR (dB/100m)		ACRF (dB/100m)		PS-ACRF (dB/100m)		Return loss (dB)
	max.	Nom.	min.	nom.	min.	Nom.	Min.	Nom.	Min.	Nom.	min.	Nom.	min.	Nom.	
1	2.1	1.9	74	78	72	75	72.0	76.1	70.0	73.1	68	82	65	80	20
4	3.8	3.8	65	69	63	66	61.2	65.2	59.2	62.2	56	70	53	68	23
10	6.0	6.0	59	63	57	60	53.0	57.0	51.0	54.0	48	62	45	60	25
16	7.6	7.6	56	60	54	57	48.4	52.3	46.4	49.3	44	58	41	56	25
20	8.5	8.5	55	59	53	56	46.5	50.0	44.5	47.0	42	56	39	54	25
31.2	10.7	10.7	52	56	50	53	41.3	45.0	39.3	42.0	38	52	35	50	23.6
62.5	15.5	15.1	47	51	45	48	31.5	36.0	29.5	33.0	32	46	29	44	21.5
100	19.9	19.1	44	48	42	45	24.1	28.9	22.1	25.9	28	42	25	40	20.1
125	22.5	21.3	43	47	41	44	20.5	25.2	18.5	22.2	26	40	23	38	19.5
155.5	25.4	23.8	42	45	40	42	16.6	21.3	14.6	18.3	24	38	21	36	18.8
175	27.1	25.3	41	44	39	41	13.9	19.1	11.9	16.1	23	37	20	35	18.4
200	29.2	27.0	40	44	38	41	10.8	16.5	8.8	13.5	22	36	19	34	18.0
250	33.0	32.0	38	42	36	39	5.0	10.0	2.0	7.0	20	34	17	32	17.3
300		36.1		41		38		4.8		1.8		32		30	
400		41.7		39		36		-2.7		-5.7		30		28	

## UC400 23 Cat. 6 U/UTP LSHF d64 Cca

### Product order data

Product code	Designation	Product name	Outer diameter mm	Euro Class	Fire load		Weight kg/km	Copper content kg/km	Tensile force N
					MJ/km	kWh/m			
60077095	J-2YH 2x4x2x0.56	UC400 23 C6 U/UTP 4P LSHF d64 Cca BU 500DW	5.9	C <sub>cas</sub> 1ad1a1	504	0.14	44	20.5	100
60077082		UC400 23 C6 U/UTP 4P LSHF d64 Cca BU 305BR		C <sub>cas</sub> 1ad1a1	504	0.14	44	20.5	100
60078193		UC400 23 C6 U/UTP 4P LSHF d64 Cca BU 1000DW		C <sub>cas</sub> 1ad1a1	504	0.14	44	20.5	100
60077095		UC400 23 C6 U/UTP 4P LSHF d64 Cca BU 250DW		C <sub>cas</sub> 1ad1a1	504	0.14	44	20.5	100

© PRYSMIAN GROUP 2012, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.