


UC1500 HS22 Cat.7_A

S/FTP AWG22/1



Application

Primary (Campus), Secondary (Riser), Tertiary (Horizontal)
IEEE 802.3: 10Base-T, 100Base-T, 1000Base-T, 10GBase-T; IEEE 802.5
ISDN, TPDDI, ATM, CATV, Broadband Video
Power over Ethernet (PoE) / Type 1-4

Standards

EN 50173-1; ISO/IEC 11801; IEC61156-5; EN50288-9-1
IEEE 802.3af / at / bt

Fire rating

EN50399: Class Eca
LSHF (LSOH): IEC 60332-1; IEC 60754-2; IEC 61034;

Construction

Conductor	Bare copper wire Ø 0.62 mm (AWG22/1)
Insulation	Foam-Skin Polyethylene, Ø 1.5 mm
Twisting	2 cores to the pair
Pair screen	Al-laminated plastic foil around each pair
Cable lay up	4 pairs
Overall screen	Copper braid, tinned
Sheath	Halogen free, flame or fire retardant sheathing material; LSHF melon yellow RAL 1028 Duplex design with divider

Mechanical Properties

Bending radius	Installation	4 x D
	Installed	8 x D
Temperature range	During operation	-20°C to + 60°C
	During installation	0°C to + 50°C

UC1500 HS22 Cat.7_A

Electrical Properties

at 20°C

DC loop resistance		≤ 128 Ω/km	
Resistance unbalance		≤ 2%	
Insulation resistance	(500 V)	≥ 5000 MΩxkm	
Capacitance	at 800 Hz	Nom. 43 nF/km	
Capacitance unbalance	(pair to ground)	≤ 1500 pF/km	
Mean characteristic impedance	@ 100 MHz	100 ± 5 Ω	
Nominal velocity of propagation		79%	
Propagation delay		450 ns/100 m	
Delay skew		15 ns/100 m	
Transfer impedance	bei 1 MHz	≤ 12 mΩ /m	Grade 2
	bei 10 MHz	≤ 10 mΩ /m	
	bei 30 MHz	≤ 30 mΩ /m	
Coupling attenuation		≥ 80 dB	Type 2
Segregation classification acc. EN 50174-2		„d“	

Nominal Transmission characteristics

acc. Cat.7_A at 20°C

F (MHZ)	Attenuation (dB/100m)	NEXT (dB)	ACR (dB/100m)	Return loss (dB)	PS-NEXT (dB)	PS-ACR (dB/100m)	ACRF (dB/100m)	PS-ACRF (dB/100m)
1	1.7	100	98	22	97	95	100	97
4	3.3	100	97	25	97	94	97	94
10	5.2	100	95	27	97	92	95	92
16	6.6	100	94	27	92	91	90	87
20	7.4	100	93	27	90	90	90	87
31.25	9.25	100	91	26	90	88	90	87
62.50	13,1	100	87	24	90	84	85	82
100	16.6	100	83	22	87	80	80	77
155	20.1	95	75	20	87	72	78	75
200	23.6	95	71	20	87	69	75	72
250	26.5	90	63	19	87	60	69	66
300	29.1	89	60	19	85	57	65	62
600	41,6	85	43	19	82	40	45	42
1000	54,0	83	29	19	80	26	40	37
1200	59,0	83	24	17	80	21	35	32
1400	63,7	81	17	15	78	14	30	27
1500	66,0	80	14	15	77	11	28	25

UC1500 HS22 Cat.7_A

Product order data

Product code	Cable type	Brand name	Outer diameter mm	Euro class	Fire load MJ/km	Weight kg/km	Copper content	Tensile force N
60022022	J-02YSCH 4x2x0.62 PiMF	UC1500 HS22 Cat.7 _A S/FTP 4P LSHF	7.6	E _{ca}	640	57	35	340
60022025	J-02YSCH 2x4x2x0.62 PIMF	UC1500 HS22 Cat.7 _A S/FTP 2x4P LSHF	7.6/15.2		1280	115	70	680

Certificates



Product Code Table

Product Description	PG Reference Code	PG Part Number
UC1500 HS22 C7A S/FTP 4P LSHF	60022022	60022022
UC1500 HS22 C7A S/FTP 4P LSHF 1000DW	60022022	60011130
UC1500 HS22 C7A S/FTP 4P LSHF 500DW	60022022	60011131
UC1500 HS22 C7A S/FTP 4P LSHF 100RW	60022022	60013287
UC1500 HS22 Cat.7A S/FTP 4P LSHF	60022022	60013288
UC1500 HS22 Cat.7A S/FTP 4P LSHF	60022022	60013289
UC1500 HS22 C7A S/FTP 2x4P LSHF	60022025	60022025
UC1500 HS22 C7A S/FTP 2x4P LSHF 500DW	60022025	60013296

© PRYSMIAN GROUP 2012, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.